

FAST, ACCURATE DETECTION OF MERCURY VAPORS

ionscience.com/usa

Pioneering Gas Sensing Technology.





ACCURATELY DETECT MERCURY VAPORS IN JUST 3 SECONDS. MVI DOES NOT SATURATE OR NEED REGENERATING ELIMINATING INSTRUMENT DOWNTIME.

Best available detection

- Fast 3 second response
- Highly accurate
- Range: 0.1 199 & 1 1999
 microgram / cubic meter
- Fast indication and recovery

Minimal downtime

- No saturation, no regeneration
 eliminates downtime
- Ready to detect within minutes
- Continuous >4.5 hour operation

Convenience

- Large, clear digital display
- Portable simple one handed operation
- Easy to use minimal training required
- Robust and withstands harsh environments
- Audible alarm gives clear indication of mercury vapors

Low cost operation

- Inexpensive consumables and parts
- 2 year warranty when instrument registered online





The Mercury Vapor Indicator (MVI) is a revolutionary instrument accurately detecting hazardous mercury vapors in just 3 seconds! The instrument's unique advantage is its dual beam UV absorption technology and ability to measure high concentrations of mercury without saturating; requiring no regeneration between readings, eliminating downtime.

Fast and accurate, MVI gives a real time response and is ready to detect in minutes. MVI provides continuous readings and offers two detection ranges: 0.1 to 199 and 1 to 1999 microgram/cubic meter, ideal for time weighted average (TWA) monitoring.

MVI is a portable mercury vapor detector that utilizes a high performance pump for fast indication and recovery. The instrument's audible alarm and large digital display clearly indicate the levels of mercury present.

Ergonomically designed with simple, one handed operation MVI is the ideal survey unit for rapid and accurate mercury detection, screening for mercury spills and monitoring for exposure limits.

Extend your instrument warranty

Your MVI instrument warranty may be extended by simply registering your product on the ION Science website within one month of purchase.

Service and Calibration

MVI requires annual calibration to maintain best accuracy, instrument performance, and to maintain its extended warranty. Contact ION Science or a local service center for more information.

Applications include:

- Manufacturing
- Recycling
- Fluorescent lamp reprocessing plants
- Mining
- Petroleum
- Hydrocarbon
- Refining
- Bioremediation

Accessories

MVI is supplied with an exclusive range of accessories. Visit ION Science website for more information.



Technical specifications

DETECTOR

 Dual Beam Ultraviolet Absorption Module

ACCURACY

• ± 5 micrograms or ± 10% reading

OPERATION

 After warm up MVI gives real time mercury vapor concentrations

ALARM

 Audible Alarm Factory pre-set to 20 microgram/cubic meter

INSTRUMENT RANGE

 0.1 to 199 and 1 to 1999 microgram cubic meter

TEMPERATURE

• 10 °C to 50 °C

WEIGHT & DIMENSIONS

- 6 lbs 10 oz (3Kgs)
- 145 x 295 x 80 mm

REPEATABILITY

• ±5% FSD @ 1 μg/m3

BATTERIES

• NiMH - last up to >4.5 hours from full charge

POWER

NiMH

RESPONSE

• <u>3 s</u>econds

MVI V1.8. This publication is not intended to form the basis of a contract and specifications can change without notice.

Distributed by:

ION Science Inc 4153 Bluebonnet drive, Stafford, Texas 77477

T Toll Free (877) 864-7710 E info@ionscienceusa.com "We rely on the Ion Science MVI with our life and the health and safety of those around us, in the extreme heat of the Middle East deserts, in the tropics of Asia, the chilling Bass Strait of Southern Australia and in extremely high levels of mercury vapour. The units must work every time, must be 100% accurate and they must be able to cope with the inevitable knocks and falls of hard use and tough environments. The MVI does that all day, every day, and has not let us down."

Director, No Heat Resources.